

RESINTECH SBG1-UPS is a narrowly graded chloride form type 1 gel strong base anion resin. *SBG1-UPS* is a uniform particle size resin with high void space and low coefficient of drag. *ResinTech SBG1-UPS* is intended for use where resin uniformity is an important attribute to help reduce pressure loss or prevent strainer plugging. *SBG1-UPS* is supplied in the chloride form or can be special ordered in the hydroxide form (when ordered as SBG1-OH-UPS).

FEATURES & BENEFITS

HIGHLY UNIFORM PARTICLE SIZE

20 to 40 mesh size, provides low pressure drop and superior kinetics

HIGH TOTAL CAPACITY

Provides long run lengths in single use applications and is ideally suited for chloride form operation

SUPERIOR PHYSICAL STABILITY

95% plus sphericity and high crush strengths together with carefully controlled particle distribution provides long life and low pressure drop

LOWER TOC LEACH RATE


Ideal for use in polishing mixed beds when ordered in the hydroxide form


COMPLIES WITH US FDA REGULATIONS

Conforms to paragraph 21CFR173.25 of the Food Additives Regulations of the US FDA

Prior to first use for potable water, resin should be backwashed for a minimum of 20 minutes, followed by 10 bed volumes of downflow rinse.

HYDRAULIC PROPERTIES





Backwash Expansion

PRESSURE LOSS

The graph above shows the expected pressure loss of *ResinTech SBG1-UPS* per foot of bed depth as a function of flow rate at various temperatures.

BACKWASH

The graph above shows the expansion characteristics of *ResinTech SBG1-UPS* as a function of flow rate at various temperatures.

RESINTECH® SBG1-UPS

PHYSICAL PROPERTIES

Polymer Structure Styrene/DVB

Polymer Type Gel

Functional Group Trimethylamine
Physical Form Spherical beads

Ionic Form as shipped Chloride or Hydroxide

Total Capacity

Hydroxide form >1.2 meq/mL Chloride form >1.3 meq/mL

Water Retention

Hydroxide form 52 to 60 percent Chloride form 42 to 51 percent

Approximate Shipping Weight

Hydroxide form 41 lbs./cu.ft.
Chloride form 44 lbs./cu.ft.
Swelling, CI to OH 18 to 25 percent

Screen Size Distribution (U.S. mesh) 20 to 40

Maximum Fines Content (<50 mesh) 0.5 percent

Minimum Sphericity 95 percent

Uniformity Coefficient 1.25 approx.

Resin Color White to amber

Note: Physical properties can be certified on a per lot basis, available upon request

SUGGESTED OPERATING CONDITIONS

Maximum continuous temperature

Hydroxide form 140°F
Chloride form 170°F
Minimum bed depth 24 inches

Backwash expansion 25 to 50 percent

Maximum pressure loss 20 psi
Operating pH range 0 to 14 SU

Regenerant Concentration

Hydroxide cycle 2 to 6 percent NaOH 2 to 10 percent NaCl Regenerant level 4 to 10 lbs./cu.ft.

Regenerant flow rate 0.25 to 1.0 gpm/cu.ft.

Regenerant contact time >40 minutes

Displacement flow rate

Displacement volume

10 to 15 gallons/cu.ft.

Rinse flow rate

Same as service flow

Rinse volume

35 to 60 gallons/cu.ft.

Service flow rate

1 to 10 gpm/cu.ft.

Note: These guidelines describe average low risk operating conditions. They are not intended to be absolute minimums or maximums.

For operation outside these guidelines, contact ResinTech Technical Support

APPLICATIONS

DEMINERALIZATION

RESINTECH SBG1-OH-UPS can be used as the anion component in a variety of demineralization applications where a hydroxide form anion resin is coupled with a hydrogen form cation resin. SBG1-OH-UPS is suitable for high operating temperatures and for high flow rates encountered in polishing condensate and other low TDS waters such as RO permeate. SBG1-OH-UPS provides low TOC and low silica leakage in ultrapure demineralizers.

PACKED BEDS

RESINTECH SBG1-UPS has a very narrow particle size range. The uniformity allows a slightly smaller bead size to be used which results in faster exchange of ions, more efficient regeneration and lower leakage. SBG1-UPS is ideal for packed beds and other types of countercurrent ion exchangers where consistent operation is important cycle after cycle. Higher void space and minimal fine mesh beads provides low pressure loss and helps prevent channeling and other distribution problems. Packed beds typically have limited freeboard (only a few inches with the resin in the swollen form).

TRACE CONTAMINANT REMOVAL (U, Cr, As, Se, ClO₄)

RESINTECH SBG1-UPS has high capacity and can be used to remove a variety of trace contaminants, even when that contaminant is not highly preferred compared to the other bulk ions in the feedwater. Useful capacities are obtained when the feedwater TDS is substantially less than the resin's internal TDS. Uranium, chromate, and perchlorate are particularly well removed. Arsenate and selenate are well removed but can be chromatographically displaced by sulfate and other ions.

NITRATE REMOVAL

RESINTECH SBG1-UPS can be used in the chloride cycle to reduce nitrates along with sulfates. Regeneration is accomplished with sodium chloride brine, in a fashion similar to water softeners. Although high operating capacities and high salt efficiency can be obtained, there is also the possibility of nitrate dumping. Use of chloride form anion resin reduces pH during the early portion of the exhaustion cycle. When treating waters with high hardness the brine dilution and displacement waters should be softened and a low hardness salt used to prevent scaling during regeneration.

SULFATE REMOVAL

High capacity resins such as *ResinTech SBG1-UPS* have high affinity for divalent anions such as sulfate, provided the feedwater TDS is not greater than about 5,000 ppm. At higher TDS the resin loses its affinity for sulfate and begins to prefer chloride. Regeneration is accomplished with sodium chloride brine in a fashion similar to a water softener.

CAUTION: DO NOT MIX ION EXCHANGE RESIN WITH STRONG OXIDIZING AGENTS. Nitric acid and other strong oxidizing agents can cause explosive reactions when mixed with organic materials, such as ion exchange resins.

MATERIAL SAFETY DATA SHEETS (MSDS) are available for all ResinTech Inc. products. To obtain a copy, contact your local ResinTech sales representative or our corporate headquarters. They contain important health and safety information.

MALERIAL SAFELY (MSDS) are available for all resinited inic. products. To obtain a copy, contact your local resinited sales representative or our corporate neadquarters. They contain important neath and safety hindration. That information may be needed to protect your employees and customers from any known health and safety hazards associated with our products. We recommend that you secure and study the pertinent MSDS for our products and any other products being used. These suggestions and data are based on information we believe to be reliable. They are offered in good faith. However we do not make any guarantee or warranty. We caution against using these products in an unsafe manner or in violation of any patents; further we assume no liability for the consequences of any such actions.

RESINTECH is a registered trademark ® of RESINTECH INC.